GYSDUCTION AUTO

Ref. 048775 - PROLINER GYSDUCTION AUTO Ref. 053380 - GYSDUCTION AUTO COMPLETE Ref. 056978 - GYSDUCTION AUTO COMPLETE +

Ref. 048812 - GYSDUCTION AUTO MECA

Ref. 056961 - GYSDUCTION AUTO MECA + Ref. 048805 - GYSDUCTION AUTO GLASS Ref. 048799 - GYSDUCTION AUTO BODY SHOP Ref. 054981 - GYSDUCTION AUTO DENT REPAIR



The GYSDUCTION AUTO is a powerful instantaneous induction heater. Ideal for car body repair, mechanics and maintenance to:

- Remove all adhesives, logos, side moldings.
- Remove direct glazed windows without damaging the trim (rear window, rear quarter light, panoramic roof...).
- Remove stone guard protection and sealers.
- Release mechanical parts (bolts, screws, spark plug, injector...).
- Repair small dents on the car body without retouching the paint.

Features

Power: 2400 W

Safety: Instant heating without flame.

Efficient: Only heats metal parts with accuracy whilst protecting the adjacent parts (no need to remove engine parts).

Clean: Remove parts without using solvent.

Flexible Voltage: Power supply from 165 V to 265 V.



BODY INDUCTOR (ref. 053359)

To quickly and easily remove all adhesives and strips as well as side moldings in a few minutes without any damage.



GLASS INDUCTOR with knob (ref. 053373)

To peel off welded metal sheets and burn off stone guard protection with the heated scraper. It is also suitable to remove glass (rear window, rear quarter light, panoramic roof...).



BOLT INDUCTOR (ref. 053366)

To warm and release all types of mechanical parts in few seconds such as bolts, screws, shock absorbers, track rod ends, etc...



DENT PULLING INDUCTOR (ref. 054776)

For the repair of light car body dents caused by hail, eliminating the need to retouch paint work.



SPIRAL (COILED / BRAIDED WIRE) INDUCTOR (ref. 054783)

To warm and release all types of mechanical parts in few seconds such as bolts, screws, shock absorbers, track rod ends, etc...



PLASTIC WEDGE (ref. 051294)

As a supplement to the inductors, the scrapers are essential to remove logos/badges and stone chip protection etc...





AUTO MODE

The device only starts if the metal is ferrous (not suitable for Aluminium or Copper). The device will then automatically adjust the heating to avoid damaging the part due to overheating.



Consumables (optional):

- 10 Logo tapes (051492)10 protections for bolt inductor + glue (053847) - 5 protections for glass inductor + glue (053854)

R		A		1/	
×	ъ.	Δ	ι.	к	•

O I ACIO											
			I						æ		
		GYSDUCTION AUTO	Plastic Wedge 051294	Glass Inductor 053373	Body Inductor 053359	Bolt Inductor 053366	Dent pulling inductor 054776	Spiral inductor 054783	Remote control 055490	Trolley SPOT 800 051331	Cable support 052284
PROLINER GYSDUCTION AUTO	ref 048775	✓	✓	✓	✓	✓	-	-	✓	✓	✓
GYSDUCTION AUTO COMPLETE	ref 053380	✓	4	✓	✓	✓	-	-	4	-	-
GYSDUCTION AUTO COMPLETE +	ref 056978	✓	✓	✓	✓	✓	-	4	4	-	-
GYSDUCTION AUTO MECA	ref 048812	✓	-	-	-	✓	-	-	~	-	-
GYSDUCTION AUTO MECA +	ref 056961	✓	-	-	-	✓	-	~	~	-	-
GYSDUCTION AUTO GLASS	ref 048805	✓	✓	✓	-	-	-	-	-	-	-
GYSDUCTION AUTO BODY SHOP	ref 048799	✓	✓	✓	4	-	✓	-	✓	-	-
GYSDUCTION AUTO DENT REPAIR	ref 054981	✓	-	-	-	-	4	-	-	-	-

50/60hz	- AM-	W	*	IP	cm	₽ kg
230 V ~1	16 A	2400	✓	21	21.5x35.5x27	7.2